



Mounting hole (inch)	0.3150"
Mounting hole (metric)	8mm
Indicator type	low cost standard
Mounting type	with bezel
Bezel type	prominent
Bezel material	plastic
Bezel color	black
Bezel size	8mm
Protection	IP40
Lens type	round
Lens color	yellow diffused
Lens size	5mm
Connector Tpe	wire terminals 450mm
Connector number	2
Connector for lamp test	no
Number LED chip	1
Indicator color	yellow
Dom wave length	588nm
Peak Wave Lenght (mA)	
Op. voltage (V)	24V DC
Forward volt max.	
Rectifier	-
AC current	-
DC current	10mA
Lum in min (mcd)	
Lum in type (DC)	25mcd
Voltage tolerance (%)	10%
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	snap in mounting
Viewing angle (°)	

Drawn : ROJ	Ch'd : ROJ	Datasheet : 19800	Print date : 09/05/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :