



Mounting hole (inch)	0.3150"
Mounting hole (metric)	8mm
Indicator type	low cost standard
Mounting type	with bezel
Bezel type	prominent
Bezel material	plastic
Bezel color	black
Bezel size	8mm
Protection	IP40
Lens type	round
Lens color	green diffused
Lens size	5mm
Connector Tpe	wire terminals 900mm
Connector number	2
Connector for lamp test	no
Number LED chip	1
Indicator color	green
Dom wave length	568nm
Peak Wave Lenght (mA)	
Op. voltage (V)	without resistor
Forward volt max.	
Rectifier	-
AC current	-
DC current	10mA
Lum in min (mcd)	
Lum in type (DC)	25mcd
Voltage tolerance (%)	-
Op. temperature (°C)	-25°C...+60°C
Storage temperature (°C)	-25°C...+60°C
Narrative	snap in mounting

Drawn : ROJ	Ch'd : ROJ	Datasheet : 19800	Print date : 09/05/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :



Part Number : 1980000051900  
Serial Number : 19800  
LEDs Indicators

Viewing angle (°)	
-------------------	--

Drawn : ROJ	Ch'd : ROJ	Datasheet : 19800	Print date : 09/05/06
Revision :	Revision date : 2006-03-15	Name : ROJ	Scale :