



JUNCTION BOX

Abox GT 025-2,5²

Abox GT 025-2,5²

Junction box

CUSTOMIZABLE

80 x 80 x 52 mm
Article number: 49240201

Junction box - Industrial Quality - with connecting terminals for encapsulating acc. DIN EN 60670 and DIN EN 60529, weather-resistant and shockproof, {zur Montage in Überschwemmungsgebieten und im Erdreich ohne Verkehrslasten}, Ui=690V, with self-sealing, soft inlet membranes, M20, seal range 2 - 16 mm, with cast resin bag 250 ml (markingfree), funnel, ventilation seals and disposable gloves, attention: note the expiration date of the cast-resin bag

grey, with screw terminal, 5-poles - 2.5 mm² (4 x 1.5² / 4 x 2.5²)



Technical data

Measures

Width:	80 mm
Length:	80 mm
Height:	52 mm

Material

Base:	polycarbonate, membrane out of TPE
Cover:	polycarbonate, glass fiber-reinforced

Accessory

- AST M20 - Attachment bushes
- BST M20 - Ventilation seal
- DMS M20 - Double-membrane seals
- GHB 1 - Cast-resin bag
- KVR M20-GDB/MGM - Cable gland
- KVR M20-MGM - Cable gland
- VST M20 - Blanking plugs
- WNI M20 - twist nipple
- WST M20 - Twist plug



JUNCTION BOX

Abox GT 025-2,5²

Entries

{Vorprägungen oben}:	2 x M20
{Vorprägungen links/rechts}:	2 x M20
{Vorprägungen unten}:	1 x M20
{Vorprägungen Rückseite}:	1 x M20

Other attributes

Entries:	8
Rated cross section:	2,5 mm ²
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Fire protection:	none
sealable:	No
Equipment:	Terminal
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP68 - acc. EN 60529 / DIN VDE 0470-1
Weatherproof:	Yes