


SWITCH - BASIC

CATALOG LISTING
BZ - 2RS - P1

FORMTEK
 FO-80376
 DRAWN
 G C H 13 APRIL 63
 CHECK
 L.S.D. / BARS 63
 REVISIONS
 A CO17410
 S C H
 13 APRIL 63
 B CO44156
 S C H
 20 APR 78
 D CO 58037
 S M A
 1 OCT 85
 E CO- 73287-G
 J A L
 20 OCT 93
 F CO- 77591
 D A W
 22 JUN 94
 G CO93346
 D L T
 11 SEP 98
 H CO- 94212-C
 D L T
 17 SEP 99
 ISSUE
 9
 DRAWING NUMBER
 M BZ-2RS-P1
 PAGE 1 OF 1
 REPLACES
 RELEASE NO.



NOTE
 ▲ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 9 - 13 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 4 OZ MIN	UL LISTED-FILE E12252 CODE L96 15A-125, 250 OR 480 VAC 1/8 HP-125 VAC; 1/4 HP-250 VAC 1/2 A-125 VDC; 1/4 A-250 VDC	UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES TOLERANCES ARE:
DIFFERENTIAL TRAVEL ----- .0004 - .0020	L288 L299 L306	ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ±
OVERTRAVEL ----- .060 MIN	16A 250V ~ T85 5E4	WEIGHT .075 LB