

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [93444-4101](#)
Status: **Active**
Overview: ML-XT™ Sealed Connection System
Description: ML-XT™ Sealed 6 Circuit Receptacle Housing, Pre-Assembled with Small Rear Seal and Cover, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-93443-001 \(PDF\)](#)

General

Product Family	Crimp Housings
Series	93444
Application	Power, Signal, Wire-to-Wire
Overview	<u>ML-XT™ Sealed Connection System</u>
Product Name	ML-XT™
UPC	889056164597

Physical

Circuits (maximum)	6
Color - Resin	Black
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	9.410/g
Number of Rows	3
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	N/A
Polarized to Mating Part	Yes
Temperature Range - Operating	-55°C to +125°C

Electrical

Current - Maximum per Contact	13A
-------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-93443-001
Sales Drawing	SD-93443-004



EU RoHS

ELV and RoHS Compliant
REACH SVHC
 Not Reviewed
Low-Halogen Status
 Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[93444Series](#)

Mates With

ML-XT™ Sealed 6 Circuit Plug Housing
[93445-4101](#)

Use With

XRC™ Female (Socket) Terminal
[84525-0009](#) (Nickel) or [84525-0032](#)
 (Selective Gold),
ML-XT™ Sealed 6
 Circuit Wedgelock Receptacle Housing
[93447-4003](#)