



**Order symbol:** TA111107  
**Product nbr:** 5814039  
**Description:** Enclosure, ABS  
**Remarks:** Grey cover

**EAN:** 6418074011473  
**EI. number:**  
 Finland: 3438268  
 Electric No. Denmark: 8212045224  
 Electric No. Sweden: 5814039

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:	
mm:	110	110	65	DRM 80	DIN-15 Mounting rail
inch:	4.3	4.3	2.6	FP 10674	
				DPS 14553	Grey sealing plug set
Materials:				Rating:	
<b>Material:</b>	ABS			Ingress Protection (EN 60529): IP65	
<b>Base colour:</b>	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
<b>Cover screws material:</b>	Polyamide			Electrical insulation: Totally insulated	
<b>Cover colour:</b>	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey			Flammability Rating: UL 94 HB	
<b>Gasket material:</b>	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 650	
Temperatures:				Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 80 °C			SGS Fimko	
<b>Temperature °C (continuous):</b>	-40 ... 60 °C				
<b>Temperature °F (short term):</b>	-40 ... 175 °F				
<b>Temperature °F (continuous):</b>	-40 ... 140 °F				
Accessories:					
MP 1111	Mounting plate				

