

**MNX PCM 150/60 G**



Sample photo

**Order symbol:** PCM 150/60 G  
**Product nbr:** 6016313  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074038074  
**EI. number:**  
 Finland: 3421640  
 Electric No. 8212027145  
 Denmark:  
 Electric No. Italy: 7341040  
 Electric No. Sweden: 2535324

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:				Accessories:	
	Length	Width	Height		
<b>mm:</b>	180	130	60	MIN 10	DIN-15 Mounting rail
<b>inch:</b>	7.1	5.1	2.4	MIN 15	DIN-15 Mounting rail
				MIV 10	DIN-35 Mounting rail
				MIV 15	DIN-35 Mounting rail
				FP A 150/180	Front plate (Aluminium)
				HFP 180	Front plate hinge series
				FP 22046	Wall fastening lug (4 pcs)
Materials:					
<b>Material:</b>	Polycarbonate				
<b>Base colour:</b>	RAL 7035 -light grey				
<b>Cover screws material:</b>	Polyamide				
<b>Cover colour:</b>	RAL 7035 -light grey				
<b>Cover screws colour:</b>	Grey				
<b>Gasket material:</b>	TPE				
Temperatures:					
<b>Temperature °C (short term):</b>	-40 ... 120 °C				
<b>Temperature °C (continuous):</b>	-40 ... 80 °C				
<b>Temperature °F (short term):</b>	-40 ... 250 °F				
<b>Temperature °F (continuous):</b>	-40 ... 175 °F				
Rating:					
Ingress Protection (EN 60529): IP66/67					
Impact Resistance (EN 62262): IK08					
Electrical insulation: Totally insulated					
Halogen free (DIN/VDE 0472, Part 815): 1					
UV resistance: UL 508					
Flammability Rating: UL 746C 5V					
Glow Wire Test (IEC 695-2-1) °C: 960					
NEMA Class: NEMA 1, 4, 4X, 6					
Certificates:					
Germanischer Lloyd (GL)					
SGS Fimko					
Gost R					
Accessories:					
MIV 150	Mounting plate (Galvanized steel)				

