

**MNX PC 175/60 HG**



Sample photo

**Order symbol:** PC 175/60 HG  
**Product nbr:** 6011319  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074022219  
**EI. number:**  
 Finland: 3420361  
 Electric No. 8212022205  
 Denmark:  
 Electric No. Italy: 7351110  
 Electric No. Sweden: 2535563

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	180	180	MIN 15	DIN-15 Mounting rail
inch:	7.1	7.1	MIV 15	DIN-35 Mounting rail
			FP A 175/180	Front plate (Aluminium)
			HFP 180	Front plate hinge series
			FP 22046	Wall fastening lug (4 pcs)
Materials:			Rating:	
<b>Material:</b>	Polycarbonate		Ingress Protection (EN 60529): IP66/67	
<b>Base colour:</b>	RAL 7035 -light grey		Impact Resistance (EN 62262): IK08	
<b>Cover screws material:</b>	Polyamide		Electrical insulation: Totally insulated	
<b>Cover colour:</b>	RAL 7035 -light grey		Halogen free (DIN/VDE 0472, Part 815): 1	
<b>Cover screws colour:</b>	Grey		UV resistance: UL 508	
<b>Gasket material:</b>	TPE		Flammability Rating: UL 746C 5V	
			Glow Wire Test (IEC 695-2-1) °C: 960	
			NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	
Temperatures:			Certificates:	
<b>Temperature °C (short term):</b>	-40 ... 120 °C		Germanischer Lloyd (GL)	
<b>Temperature °C (continuous):</b>	-40 ... 80 °C		SGS Fimko	
<b>Temperature °F (short term):</b>	-40 ... 250 °F		Gost R	
<b>Temperature °F (continuous):</b>	-40 ... 175 °F			
Accessories:				
MIV 175	Mounting plate (Galvanized steel)			

