

MNX PC 175/75 HG



Sample photo

Order symbol: PC 175/75 HG
Product nbr: 6011320
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074024411
EI. number:
 Finland: 3422252
 Electric No. Denmark: 8212022645
 Electric No. Italy: 7351113
 Electric No. Sweden: 2535564

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Length	Width	Height	Accessories:	
mm:	180	180	75			MIN 15	DIN-15 Mounting rail
inch:	7.1	7.1	3.0			MIV 15	DIN-35 Mounting rail
Materials:							
Material:	Polycarbonate				FP A 175/180	Front plate (Aluminium)	
Base colour:	RAL 7035 -light grey				HFP 180	Front plate hinge series	
Cover screws material:	Polyamide				FP 22046	Wall fastening lug (4 pcs)	
Cover colour:	RAL 7035 -light grey				Rating:		
Cover screws colour:	Grey				Ingress Protection (EN 60529): IP66/67		
Gasket material:	TPE				Impact Resistance (EN 62262): IK08		
Temperatures:							
Temperature °C (short term):	-40 ... 120 °C				Electrical insulation: Totally insulated		
Temperature °C (continuous):	-40 ... 80 °C				Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):	-40 ... 250 °F				UV resistance: UL 508		
Temperature °F (continuous):	-40 ... 175 °F				Flammability Rating: UL 746C 5V		
Accessories:							
MIV 175	Mounting plate (Galvanized steel)				Glow Wire Test (IEC 695-2-1) °C: 960		
					NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
					Certificates:		
					Germanischer Lloyd (GL)		
					SGS Fimko		
					Gost R		

