

MNX PC 200/100 HG



Sample photo

Order symbol: PC 200/100 HG
Product nbr: 6011327
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022240
EI. number:
 Finland: 3420373
 Electric No. 8212022234
 Denmark:
 Electric No. Italy: 7351125
 Electric No. Sweden: 2535572

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	255	180	100
inch:	10.0	7.1	3.9

Materials:	
Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	TPE

Temperatures:	
Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:	
MIV 200	Mounting plate (Galvanized steel)

Accessories:	
MIN 15	DIN-15 Mounting rail
MIN 20	DIN-15 Mounting rail
MIV 15	DIN-35 Mounting rail
MIV 20	DIN-35 Mounting rail
FP A 200/180	Front plate (Aluminium)
HFP 180	Front plate hinge series
FP 22046	Wall fastening lug (4 pcs)

Rating:	
Ingress Protection (EN 60529): IP66/67	
Impact Resistance (EN 62262): IK08	
Electrical insulation: Totally insulated	
Halogen free (DIN/VDE 0472, Part 815): 1	
UV resistance: UL 508	
Flammability Rating: UL 746C 5V	
Glow Wire Test (IEC 695-2-1) °C: 960	
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13	

Certificates:	
Germanischer Lloyd (GL)	
SGS Fimko	
Gost R	

