

**MNX PC 200/88 XHG**



Sample photo

**Order symbol:** PC 200/88 XHG  
**Product nbr:** 6013330  
**Description:** Enclosure, PC  
**Remarks:** Grey cover

**EAN:** 6418074051936  
**EI. number:**  
 Finland: 3435262  
 Electric No. 8212022878  
 Denmark:  
 Electric No. Sweden: 6013330

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	255	180	88	MIN 15 DIN-15 Mounting rail
inch:	10.0	7.1	3.5	MIN 20 DIN-15 Mounting rail
				MIV 15 DIN-35 Mounting rail
				MIV 20 DIN-35 Mounting rail

**Materials:**

**Material:** Polycarbonate

**Base colour:** RAL 7035 -light grey

**Cover screws material:** Polyamide

**Cover colour:** RAL 7035 -light grey

**Cover screws colour:** Grey

**Gasket material:** Polyurethane

**Accessories:**

FP A 200/180 Front plate (Aluminium)

HFP 180 Front plate hinge series

FP 22046 Wall fastening lug (4 pcs)

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C

**Temperature °C (continuous):** -40 ... 80 °C

**Temperature °F (short term):** -40 ... 250 °F

**Temperature °F (continuous):** -40 ... 175 °F

**Rating:**

Ingress Protection (EN 60529): IP66/67

Impact Resistance (EN 62262): IK08

Electrical insulation: Totally insulated

Halogen free (DIN/VDE 0472, Part 815): 1

UV resistance: UL 508

Flammability Rating: UL 746C 5V

Glow Wire Test (IEC 695-2-1) °C: 960

NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

**Accessories:**

MIV 200 Mounting plate (Galvanized steel)

**Certificates:**

Germanischer Lloyd (GL)

SGS Fimko

Gost R

