

Capacitor, film, 0.047 uF, +/-10% Tol, -40/+110C, Safety: X1, 440 VAC, Lead Spacing=22.5 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	26.50	+0.3
H	13.50	+0.1
T	6.50	+0.2
S	22.50	+/-0.4
LL	25.00	+2/-1
F	0.80	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	500

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Safety: X1
Sub Application:	AEC-Q200
Style:	Radial Box
Approvals:	ENEC,UL,cUL
RoHS:	Yes

Specifications	
Capacitance:	0.047 uF
Voltage:	1000 VDC
Tolerance:	+/-10%
Voltage AC:	440 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	0.1%
Insulation Resistance:	100 GOhm
Maximum dVdT:	300 v/us