

OmniSmart 1500VA 2U Rack/Tower Line-Interactive 120V UPS with LCD display and USB port

MODEL NUMBER: **OMNI1500LCD**



Description

Tripp Lite's OMNI1500LCD Line-Interactive Digital UPS System offers voltage regulation, surge suppression and long-lasting battery support for personal computers, and small business network applications. Automatic Voltage Regulation (AVR) circuits regulate brownouts and overvoltages from 75V to 147V back to usable levels without using battery power. Offers complete power protection with support for upright tower 2U rackmount installation in an attractive all-black cabinet design. Includes 6 battery-supported outlets plus 2 additional surge suppression only outlets for devices not requiring battery support. Built-in USB port enables optional unattended system shutdown without data loss in case of extended power failure; cable included. PowerAlert software available via free download from www.tripplite.com. HID-compliant USB interface enables integration with built-in power management and auto shutdown features of Windows and Mac OS X. Built-in single-line RJ-45 jacks offer protection for equipment with single-line tel/DSL or network Ethernet connection. Built-in audible alarm and large LCD front panel voltage display indicates line power status, battery power status, battery low/replace status and voltage regulation operation. The LCD display includes a dimmer switch and can be rotated for easy viewing in horizontal or vertical placement. 1500VA power-handling capacity supports entry-level PCs, home entertainment systems, network workstations and audio/video components. Offers 2.5 minutes battery runtime at full load of 1500VA and 9 minutes at 750VA. \$200,000 [connected equipment insurance](#) (USA, Puerto Rico and Canada only).

Features

- LCD Display indicates input voltage, battery capacity and a variety of operating conditions. Display is rotatable for easy viewing whether UPS is in vertical or horizontal position
- OMNI1500LCD Digital Uninterruptible Power Supply offers voltage regulation, surge suppression and long-lasting battery support during blackouts
- Regulates brownouts and overvoltages from 75V to 147V back to usable levels without using battery power
- 6 UPS battery-supported outlets for critical items, plus 2 additional surge suppression-only outlets for accessories not requiring battery support
- Included USB monitoring port and cable enables unattended shutdown in the case of extended power failure
- HID-compliant USB port enables integration with built-in power management and auto shutdown features of Windows and Mac OS X
- PowerAlert software available via free download from www.tripplite.com
- Set of phone/network protection jacks protects a single dialup/DSL phone line or network Ethernet connection
- 1500VA/825W power handling ability supports a variety of electronic equipment
- 2.5 min. full load runtime (1500VA/825W); 9 min. half-load runtime (750VA/413W)

Highlights

- 1500VA / 1.5kVA 2U rack/tower 120V line interactive UPS with LCD display
- Corrects brownouts and overvoltages from 75V to 147V
- LCD screen reports input voltage, battery charge and UPS status
- USB, TEL/DSL/ethernet protection, Surge-only outlets, Rackmount kit
- NEMA 5-15P input plug and 8 NEMA 5-15R outlets

Package Includes

- OMNI1500LCD UPS System
- USB Cable
- Phone Cable
- Rackmount brackets
- Instruction manual



- Cabinet adapts to tower or rackmount shelf format. Rackmount installation brackets for 2U installation included
- \$200,000 [connected equipment insurance](#) (USA, Puerto Rico and Canada only).

Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	1500
Output kVA Capacity (kVA)	1.5
Output Watt Capacity (Watts)	825
Nominal Output Voltage(s) Supported	115V; 120V
Frequency Compatibility	60 Hz
Output Voltage Regulation (Line Mode)	-18%, +8%
Output Voltage Regulation (Battery Mode)	115V (+/- 5%)
Output Receptacles	(8) 5-15R
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 2 surge-only outlets
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
INPUT	
Rated input current (Maximum Load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
Input Circuit Breakers	10A
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full Load Runtime (min.)	2.5 min. (825w)
Half Load Runtime (min.)	9 min. (413w)
DC System Voltage (VDC)	24
Battery Recharge Rate (Included Batteries)	Less than 3.5 hours from 10% to 90%
VOLTAGE REGULATION	



Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with an input voltage range of 75 to 147
Overvoltage Correction	Input voltages between 128 and 147 are reduced by 12%
Undervoltage Correction	Input voltages between 93 and 107 are boosted by 14%
Severe Undervoltage Correction	Input voltages between 75 and 92 are boosted by 30%
LEDS ALARMS & SWITCHES	
LED Indicators	Front panel LCD display
Front Panel LCD Display	Backlighted LCD screen indicates input voltage, 5-bar battery charge level, overload, AVR, on battery and replace battery status; LCD screen rotates for rack/tower viewing
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation; dimmer switch controls LCD brightness
SURGE / NOISE SUPPRESSION	
UPS AC Suppression Joule Rating	420
UPS AC Suppression Response Time	Instantaneous
UPS Dataline Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
PHYSICAL	
Installation Form Factors Supported with Included Accessories	2 post 19 inch rackmount; 4 post 19 inch rackmount; Tower
Included Mounting Accessory Description	Pair of mounting ears enable tower and 2-4 post rackmount installation
Primary Form Factor	Rackmount
UPS Power Module Dimensions (hwd, in.)	3.5 x 17.2 x 10.5
UPS Power Module Dimensions (hwd, cm)	8.9 x 43.8 x 26.7
Installed Whole System Maximum Rack Depth (in.)	10.5
Installed Whole System Maximum Rack Depth (cm)	26.7
Rack Height (U Spaces)	2
UPS Power Module Weight (lbs.)	29.4
UPS Power Module Weight (kg)	13.3
UPS Shipping Dimensions (hwd / in.)	7.5 x 15 x 21.5
UPS Shipping Dimensions (hwd / cm)	19 x 38.1 x 54.6



Shipping Weight (lbs.)	33.4
Shipping Weight (kg)	15.2
Cooling Method	Fan
UPS Housing Material	ABS
ENVIRONMENTAL	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC Mode BTU / Hr. (Full Load)	140
AC Mode Efficiency Rating (100% Load)	95%
COMMUNICATIONS	
Communications Interface	USB (HID enabled)
Network Monitoring Port Description	Supports detailed monitoring of UPS and site power conditions
PowerAlert Software	Free download from www.tripplite.com
Communications Cable	USB cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
LINE / BATTERY TRANSFER	
Transfer Time	4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	75
High Voltage Transfer to Battery Power (Setpoint)	147
SPECIAL FEATURES	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
CERTIFICATIONS	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI); Meets FCC Part 68 / Industrie Canada (telecommunications)
WARRANTY	
Product Warranty Period (U.S. & Canada)	3-year limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Product Warranty Period (Puerto Rico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.