

810 SCOTCH™ MAGIC™

DESCRIPTION :

A tape that is frosty in appearance on the roll, yet invisible on most papers.



CHARACTERISTICS :

Backing	: Matte acetate of cellulose
Adhesive	: Synthetic acrylics
Adhesion to steel	: 2,5 N/cm
Tensile strength	: 2,7 daN/cm
Elongation at break	: 25 %
Total tape thickness	: 0,0625 mm
pH value	: 5,8 (slightly acid)

PRODUCT FORMS :

Rolls in 33 meters and 66 meters long, having numerous widths
Pad: 25 strips of 19 x 76 mm

USES :

- . Mending tracings, drawings, library books, blue print, legal documents, and other permanent applications.
- . Sealing envelopes
- . Assembling

PRODUCT BENEFITS :

- . **Invisibility on white paper and copy**
- . **Extremely long aging: Non tape yellowing**
Non adhesive staining
- . **Very easy tear**
- . **Low, smooth and unnoisy roll unwind**
- . **Good adhesion**
- . **Moisture resistant**
- . **Write on surface, with any writing media**
- New ™ . **Green core: pro-environmental consideration, due to its solvent free manufacturing process.**