

# WAGO 890-702



## Socket Snap-in version 2-pole

Product group	20 (WINSTA)
pole count	2
Cross section [mm <sup>2</sup> ]	0.25 - 1.5 mm <sup>2</sup>
Cross section [AWG]	22 - 16 AWG
Connection method	CAGE CLAMP®S Connection
Measured voltage EN	250 V
Measured shock voltage	4 kV
Pollution degree	3
Current intensity EN	16 A
Weight	4.476 g
Color	black
No. of connection Points	2
No. of potentials	2
Height	16 mm
Height	0.63 in
Width	19.8 mm
Width	0.78 in
Depth	39.85 mm
Depth	1.569 in
Strip length from	9 mm
Strip length to	9 mm
Strip length	0.35 in
Customs Tariff No.	85366990
Country of Origin	Deutschland