

LG IPS MONITOR MP57

24MP57VQ

COLLAPSE ALL SPECS

GENERAL

Screen size (inches)	23.8
Panel Type	IPS
Aspect Ratio	16:9
Resolution	1920 x 1080
Brightness (cd/m2)	250
Contrast Ratio	5000000:1
Response Time (ms)	5
Viewing Angle (°)	178 /178 (CR≥10)
Colour Depth (Num of Colours)	16.7M
Pixel Pitch (mm)	0.2745 x 0.2745
Colour Gamut	72% (CIE1976)
Surface Treatment	Anti-Glare,3H

INPUT / OUTPUT

D-Sub	Yes
DVI-D	Yes
HDMI	Yes
Audio Output	Headphone Out

FEATURES

DDC/CI	Yes
HDCP	Yes
Intelligent Auto	Yes
Plug & Play	Yes
Response Time Control	Yes
Key Lock	Yes

SPECIAL FEATURES

4 screen split	Yes
Flicker safe	Yes
Super+ Resolution	Yes
SIX Axis Control	Yes
Colour Cloning	Yes
Colour Wizard	Yes
Automatic Standby	Yes

STAND

Base detachable	Yes
Tilt(Angle)	Yes: -5° ~ 20° Degree

STANDARD (CERTIFICATION) & VESA MOUNTING

TCO6.0	Yes
UL(cUL)	Yes
TUV-Type	Yes
FCC-B, CE	Yes

POWER

Type / Input	Adaptor / 100~240V
Consumption Normal On (Typ.)	26W
Normal On(EPA)	22W
Consumption Power Save/Sleep Mode(Max)	0.3W
DC Off (Max)	0.3W

DIMENSIONS - WDXH (MM)

Set (with Stand)	555 x 195 x 436
Set (without Stand)	555 x 65 x 339
Box Dimension	623 x 404 x 119

WEIGHT(KG)

Set with Stand (Kg)	3.2
---------------------	-----

Set without Stand (Kg)
Shipping Weight (Kg)

2.9
4.4
