

Model 1015

For use in plant and field service applications and harsh environments



► FEATURES

- True Megohmmeter®
- Test voltage selections of 500V or 1000V
- Insulation measurements to 1000MΩ
- Push button for battery check
- Resistance range to 1000Ω
- 0 to 10Ω- and 0 to 10Ω+ continuity ranges
- Continuity measurements with 200mA test current
- Compact and lightweight
- Large, direct-reading and colored scale
- 600V test voltage range (safety check)
- Includes a yellow, non-slip, shockproof rubber housing and soft carrying case

► SPECIFICATIONS

MODEL	1015	
INSULATION TESTS		
Test Voltage	500V 1000V	0.1 to 1000MΩ 0.1 to 1000MΩ
Short Circuit Current		≤6mA (max)
Accuracy		±5% of Reading
Voltage Test/Safety Check		0 to 600Vac
RESISTANCE TESTS		
Measurement Range		0 to 1000Ω
Short Circuit Current		≥2mA
Open Circuit Voltage		4.5 to 6.5V
Accuracy		±3% of Full Scale
CONTINUITY TESTS		
Measurement Range		0 to 10Ω-; 0 to 10Ω+
Short Circuit Current		≥200mA
Open Circuit Voltage		4.5 to 6.5V
Accuracy		±3% of Full Scale
VOLTAGE TESTS		
Measurement Range		0 to 600Vac
Frequency		45 to 400Hz
Accuracy		±3% of Full Scale
Input Impedance		300kΩ
ELECTRICAL		
Power Source		4 x 1.5V AA Alkaline batteries (included)

► PRODUCT INCLUDES



Shockproof rubber housing, one set of black and red leads, one black test probe, one red alligator clip, spare fuse (inside Megohmmeter), four 1.5V Alkaline AA batteries, soft carrying case and user manual.

CATALOG NO.	DESCRIPTION
1403.01	Megohmmeter Model 1015 (Analog, 500V, 1000V, Resistance, Continuity)