



RE1220-LF

- Epoxy fibre-glass FR4 0.80 mm
- Single-sided 35 µm Cu
- Without holes
- Hot air leveling (HAL-leadfree)
- 12 self-adhesive strips with square-pads in parallel order
- Pre-scratched rated break point for the separation of individual modules from the board
- Size 90 x 100 mm



RE1220-LF


- Epoxydglashartgewebe FR4 0,80 mm
- Einseitig 35 µm Cu
- Keine Bohrungen
- Heißverzinkt (HAL-leadfree)
- 12 selbstklebende Kontakteleisten mit parallel angeordneten quadratischen Pads
- Vorgeritzte Sollbruchstellen
- Größe 90 x 100 mm



RE1220-LF

- Fibre de verre époxyde FR4 0,80 mm
- Simple face 35 µm Cu
- Sans trous
- Étamée à chaud (HAL-leadfree)
- 12 listeaux de contact autoadhésifs avec pastilles carrées placées en parallèle
- Points destinés à la rupture
- Dimensions 90 x 100 mm

ver.20150130



RE1220-LF

- Fibra de vidrio epoxídica FR4 0,80 mm
- Por dos lados 35 µm de Cu
- Sin agujeros
- Estañado en caliente (HAL-leadfree)
- 12 adaptadores autoadhesivos con pads cuadrados dispuestos en paralelo
- Punto de rotura controlada tallado
- Tamaño 90 x 100 mm