



#### RE2011-LF

- Epoxy fibre-glass FR4 1.50 mm
- Without Cu
- Hole spacing 2.54 x 2.54 mm
- 38 x 61 holes with 1.00 mm Ø
- Size 100 x 160 mm



**RE2011-LF**

- Epoxydglashartgewebe FR4 1,50 mm
- Ohne Cu
- Lochraster 2,54 x 2,54 mm
- 38 x 61 Bohrungen 1,00 mm Ø
- Größe 100 x 160 mm



#### RE2011-LF

- Fibre de verre époxyde FR4 1,50 mm
- Sans Cu
- Pas 2,54 x 2,54 mm
- 38 x 61 trous 1,00 mm Ø
- Dimensions 100 x 160 mm



#### RE2011-LF

- Fibra de vidrio epoxídica FR4 1,50 mm
- Sin Cu
- Trama de agujeros 2,54 x 2,54 mm
- 38 x 61 agujeros 1,00 mm Ø
- Tamaño 100 x 160 mm