


0.050	FLOATIONIO				
SPECIFICATIONS					
CONTACT CARRIER MATERIAL	NYLON OR TPU				
MOLDED HEAD MATERIAL/COLOR	ELASTOLLAN 1195A/CLEAR				
CONTACT MATERIAL/PLATING	BRASS/GOLD				
COUPLING NUT MATERIAL/PLATING	BRASS/NICKEL				
RATED CURRENT [A]	4.0 A				
RATED VOLTAGE [V]	10-30 VDC				
OUTER CABLE JACKET MATERIAL/COLOR	PVC/GRAY				
CONDUCTOR INSULATION MATERIAL	PVC				
NUMBER OF CONDUCTORS [AWG]	3x22 AWG				
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)				
PROTECTION CLASS	NEMA 1,3,4,6P AND IEC IP68, IP69K				



CABLE LENGTH	TOLERANCE *					
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER					
STRIP LENGTH	TOLERANCE *					
0-7mm	±0.5mm					
8-29mm	±1.0mm					
30-49mm	±2.0mm					
50-69mm	±3.0mm					
70-100mm	±4.0mm					
OVER 100mm	±5.0mm					
* UNLESS OTHERWISE SPECIFIED						

NOTES:

REV DESCRIPTION

UPDATE CABLE SPECIFICATIONS

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.

			RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS CONFIDENTIAL AND THE PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technology	MINNEAPO 1-800 (763) (763)	3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com			
C TO ORDER			MATERIAL		DRFT RWC	DATE 12/20/06	DESCRIPTION	- 4T-*-P7X2	: D7V2		
			SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS	APVD	SCALE 1=1.0	KNE	41-*//			
				DRAWING ARE FOR REFERENCE ONLY	UNIT OF ME	ASUREMENT	IDENTIFICATION NO.			004	
			FINISH	Н						REV	
				CONTACT TURCK FOR MORE	MILLIMETER [INCH]					FI	
1	KMY	05/22/14	44672	SEE SPECIFICATIONS	INFORMATION						'
T	BY	DATE	ECO NO.			DO NOT SCALE	THIS DRAWING	FILE: 777002595		SHEET	1 OF 1

SOURCE DRAWING - FOR REFERENCE ONLY