

## Black Box Products

### Cables > Computer & Data Cables

#### Extended-Distance Data Cable with Removable Hoods, 25 Conductors (12 1/2 Pairs), 250-ft., M/M

Shielded cable with removable hoods for repinning.  
EDN25C-0250-MM

##### **Product Highlights**

- Features an aluminum-foil shield for EMI/RFI protection and a drain wire.
- Repinnable.
- Transmit RS-232 data up to 500 feet at 9600 bps
- All conductors are straight wired.
- Guaranteed for life!

##### **Further Details**

- NEC® CL2 compliant. Not for use in risers or plenums.
- Low capacitance.
- Male screw locks are standard.



<b>Cable Construction</b>	PVC
<b>Capacitance</b>	12 pF/ft. ± 2 pF/ft.
<b>Conductor Gauge</b>	24 AWG (7 x 32), stranded
<b>Outside Diameters</b>	0.430"
<b>Resistance</b>	30 ohms/1000 ft.

NOTE: For plenum cable, contact our FREE Tech Support.

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight. For shipping weight, please contact Black Box customer service at 1-800-316-7107.