

Black Box Products

Industrial > Cabling & Infrastructure

Bulk Extended-Distance/Quiet Cable, Industrial Environment, PVC Jacket, 16 Conductors (8 Pairs), 500-ft. (152.4-m)

Send RS-232 data up to 500 feet in noisy environments.

EMN16A-0500



Product Highlights

- Ideal for noisy environments where cable runs are next to power lines and other cabling systems that cause interference.
- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!

Cable Type	Twisted pair, PVC jacket
Capacitance	12 pF/ft. ± 2 pF/ft.
Conductor Gauge	24 AWG (7 x 32 AWG) stranded
Resistance	25 ohms/1000 ft.
Shield	One foil and one copper braid

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight. For shipping weight, please contact Black Box customer service at 1-800-316-7107.