

15 Amp Vertical Rackmount Outlet Strip *1585-6-7-8*

Series



Features

- Designed to have a low-profile our strips are just 1 5/8" wide by 1 3/8" high.
- Constructed of rugged light weight aluminum.
- Designed for a variety of applications:
 - Install in your server cabinets
 - Wall mount cabinets
 - Open frame racks
 - Or install horizontally above your work bench.
- Each outlet strip included a hardware mounting kit. Order P/N: **1585CLIP** for additional hardware kit.
- Receptacles are 1" square and are equally spaced over the length of the power strip.
- With on/off switch or pilot light and 15 Amp circuit breaker.
- Plug type available is a NEMA 5-15P straight blade.
- **Click here for our surge protected version.**

Specifications

- Heavy duty 14 gauge wire cord - 14/3 SJT type for extreme temperature ranges and integral molded plug.
- Plug types available are NEMA 5-15P straight blade or NEMA L5-15P locking type.
- Rated 15 amps, 120 volts.
- CSA certified, Standards C22.2 (No. 21-95 and No. 42-99)
- UL listed, Standard UL1363 - file # E166039
- NOTE #1: Outlet strips can NOT be used between the front & rear panel rails of rack cabinets as they (and the equipment plugs) will interfere with mounted equipment and mounted accessories.
- NOTE #2: To properly use on rack cabinets, allow sufficient depth BEHIND the rear panel rails for vertically mounting to the cabinet.

Accessories

- Vertical Outlet Strip Mounting Clip Kit

| Part No. On-Off Switch | Part No. Pilot Light | Strip Length | Number of Outlets | Surge Protected | Cord Length (ft) | Color | NEMA Plug Type |
|---------------------------|-------------------------|-----------------|----------------------|--------------------|---------------------|---------|-------------------|
| 15851H6A1 | 15851T6A1 | 18.00 | 6 | No | 6 | Natural | 5-15P |
| 15851H6B1 | 15851T6B1 | 18.00 | 6 | No | 15 | Natural | 5-15P |
| 15851H6C1 | 15851T6C1 | 18.00 | 6 | No | 6 | Natural | L5-15P |
| 15851H6D1 | 15851T6D1 | 18.00 | 6 | No | 15 | Natural | L5-15P |
| 15852H6A1 | 15852T6A1 | 24.00 | 6 | No | 6 | Natural | 5-15P |

| Part No. On-Off Switch | Part No. Pilot Light | Strip Length | Number of Outlets | Surge Protected | Cord Length (ft) | Color | NEMA Plug Type |
|---|---------------------------------------|-------------------------------|------------------------------------|----------------------------------|-----------------------------------|--------------|---------------------------------|
| 15852H6B1 | 15852T6B1 | 24.00 | 6 | No | 15 | Natural | 5-15P |
| 15852H6C1 | 15852T6C1 | 24.00 | 6 | No | 6 | Natural | L5-15P |
| 15852H6D1 | 15852T6D1 | 24.00 | 6 | No | 15 | Natural | L5-15P |
| 15852H8A1 | 15852T8A1 | 24.00 | 8 | No | 6 | Natural | 5-15P |
| 15852H8B1 | 15852T8B1 | 24.00 | 8 | No | 15 | Natural | 5-15P |
| 15852H8C1 | 15852T8C1 | 24.00 | 8 | No | 6 | Natural | L5-15P |
| 15852H8D1 | 15852T8D1 | 24.00 | 8 | No | 15 | Natural | L5-15P |
| 15853H6A1 | 15853T6A1 | 36.00 | 6 | No | 6 | Natural | 5-15P |
| 15853H6B1 | 15853T6B1 | 36.00 | 6 | No | 15 | Natural | 5-15P |
| 15853H6C1 | 15853T6C1 | 36.00 | 6 | No | 6 | Natural | L5-15P |
| 15853H6D1 | 15853T6D1 | 36.00 | 6 | No | 15 | Natural | L5-15P |
| 15854H7A1 | 15854T7A1 | 42.00 | 7 | No | 6 | Natural | 5-15P |
| 15854H7B1 | 15854T7B1 | 42.00 | 7 | No | 15 | Natural | 5-15P |
| 15854H7C1 | 15854T7C1 | 42.00 | 7 | No | 6 | Natural | L5-15P |
| 15854H7D1 | 15854T7D1 | 42.00 | 7 | No | 15 | Natural | L5-15P |
| 1585H8A1 | 1585T8A1 | 48.00 | 8 | No | 6 | Natural | 5-15P |
| 1585H8A1BK | 1585T8A1BK | 48.00 | 8 | No | 6 | Black | 5-15P |
| 1585H8B1 | 1585T8B1 | 48.00 | 8 | No | 15 | Natural | 5-15P |
| 1585H8B1BK | 1585T8B1BK | 48.00 | 8 | No | 15 | Black | 5-15P |
| 1585H8C1 | 1585T8C1 | 48.00 | 8 | No | 6 | Natural | L5-15P |
| 1585H8D1 | 1585T8D1 | 48.00 | 8 | No | 15 | Natural | L5-15P |
| 1585H10A1 | 1585T10A1 | 48.00 | 10 | No | 6 | Natural | 5-15P |
| 1585H10B1 | 1585T10B1 | 48.00 | 10 | No | 15 | Natural | 5-15P |
| 1585H10C1 | 1585T10C1 | 48.00 | 10 | No | 6 | Natural | L5-15P |
| 1585H10D1 | 1585T10D1 | 48.00 | 10 | No | 15 | Natural | L5-15P |
| 1585H11A1 | 1585T11A1 | 48.00 | 11 | No | 6 | Natural | 5-15P |
| 1585H11B1 | 1585T11B1 | 48.00 | 11 | No | 15 | Natural | 5-15P |
| 1585H11C1 | 1585T11C1 | 48.00 | 11 | No | 6 | Natural | L5-15P |
| 1585H11D1 | 1585T11D1 | 48.00 | 11 | No | 15 | Natural | L5-15P |
| 1585H15A1 | 1585T15A1 | 48.00 | 15 | No | 6 | Natural | 5-15P |
| 1585H15B1 | 1585T15B1 | 48.00 | 15 | No | 15 | Natural | 5-15P |
| 1585H15C1 | 1585T15C1 | 48.00 | 15 | No | 6 | Natural | L5-15P |
| 1585H15D1 | 1585T15D1 | 48.00 | 15 | No | 15 | Natural | L5-15P |
| 1585H16A1 | 1585T16A1 | 48.00 | 16 | No | 6 | Natural | 5-15P |
| 1585H16B1 | 1585T16B1 | 48.00 | 16 | No | 15 | Natural | 5-15P |
| 1585H16C1 | 1585T16C1 | 48.00 | 16 | No | 6 | Natural | L5-15P |
| 1585H16D1 | 1585T16D1 | 48.00 | 16 | No | 15 | Natural | L5-15P |
| 1586H10A1 | 1586T10A1 | 60.00 | 10 | No | 6 | Natural | 5-15P |
| 1586H10B1 | 1586T10B1 | 60.00 | 10 | No | 15 | Natural | 5-15P |
| 1586H10C1 | 1586T10C1 | 60.00 | 10 | No | 6 | Natural | L5-15P |
| 1586H10D1 | 1586T10D1 | 60.00 | 10 | No | 15 | Natural | L5-15P |
| 1586H12A1 | 1586T12A1 | 60.00 | 12 | No | 6 | Natural | 5-15P |
| 1586H12A1BK | 1586T12A1BK | 60.00 | 12 | No | 6 | Black | 5-15P |
| 1586H12B1 | 1586T12B1 | 60.00 | 12 | No | 15 | Natural | 5-15P |
| 1586H12B1BK | 1586T12B1BK | 60.00 | 12 | No | 15 | Black | 5-15P |
| 1586H12C1 | 1586T12C1 | 60.00 | 12 | No | 6 | Natural | L5-15P |
| 1586H12D1 | 1586T12D1 | 60.00 | 12 | No | 15 | Natural | L5-15P |
| 1587H10A1 | 1587T10A1 | 70.00 | 10 | No | 6 | Natural | 5-15P |
| 1587H10A1BK | 1587T10A1BK | 70.00 | 10 | No | 6 | Black | 5-15P |
| 1587H10B1 | 1587T10B1 | 70.00 | 10 | No | 15 | Natural | 5-15P |
| 1587H10B1BK | 1587T10B1BK | 70.00 | 10 | No | 15 | Black | 5-15P |
| 1587H10C1 | 1587T10C1 | 70.00 | 10 | No | 6 | Natural | L5-15P |
| 1587H10D1 | 1587T10D1 | 70.00 | 10 | No | 15 | Natural | L5-15P |

| Part No. On-Off Switch | Part No. Pilot Light | Strip Length | Number of Outlets | Surge Protected | Cord Length (ft) | Color | NEMA Plug Type |
|-----------------------------------|---------------------------------|-------------------------|------------------------------|----------------------------|-----------------------------|--------------|---------------------------|
| 1587H11A1 | 1587T11A1 | 70.00 | 11 | No | 6 | Natural | 5-15P |
| 1587H11B1 | 1587T11B1 | 70.00 | 11 | No | 15 | Natural | 5-15P |
| 1587H11C1 | 1587T11C1 | 70.00 | 11 | No | 6 | Natural | L5-15P |
| 1587H11D1 | 1587T11D1 | 70.00 | 11 | No | 15 | Natural | L5-15P |
| 1587H12A1 | 1587T12A1 | 70.00 | 12 | No | 6 | Natural | 5-15P |
| 1587H12B1 | 1587T12B1 | 70.00 | 12 | No | 15 | Natural | 5-15P |
| 1587H12C1 | 1587T12C1 | 70.00 | 12 | No | 6 | Natural | L5-15P |
| 1587H12D1 | 1587T12D1 | 70.00 | 12 | No | 15 | Natural | L5-15P |
| 1587H19A1 | 1587T19A1 | 70.00 | 19 | No | 6 | Natural | 5-15P |
| 1587H19B1 | 1587T19B1 | 70.00 | 19 | No | 15 | Natural | 5-15P |
| 1587H19C1 | 1587T19C1 | 70.00 | 19 | No | 6 | Natural | L5-15P |
| 1587H19D1 | 1587T19D1 | 70.00 | 19 | No | 15 | Natural | L5-15P |
| 1587H24A1 | 1587T24A1 | 70.00 | 24 | No | 6 | Natural | 5-15P |
| 1587H24B1 | 1587T24B1 | 70.00 | 24 | No | 15 | Natural | 5-15P |
| 1587H24C1 | 1587T24C1 | 70.00 | 24 | No | 6 | Natural | L5-15P |
| 1587H24D1 | 1587T24D1 | 70.00 | 24 | No | 15 | Natural | L5-15P |
| 1588H12A1 | 1588T12A1 | 77.00 | 12 | No | 6 | Natural | 5-15P |
| 1588H12A1BK | 1588T12A1BK | 77.00 | 12 | No | 6 | Black | 5-15P |
| 1588H12B1 | 1588T12B1 | 77.00 | 12 | No | 15 | Natural | 5-15P |
| 1588H12B1BK | 1588T12B1BK | 77.00 | 12 | No | 15 | Black | 5-15P |
| 1588H12C1 | 1588T12C1 | 77.00 | 12 | No | 6 | Natural | L5-15P |
| 1588H12D1 | 1588T12D1 | 77.00 | 12 | No | 15 | Natural | L5-15P |

Data subject to change without notice