

Universal Power Extension Cord Y Splitter Cable (NEMA 5-15P to 2x IEC-320-C13), 6-ft.

MODEL NUMBER: P006-006-2



Highlights

- Connect two devices to one power outlet
- Plug type - NEMA 5-15P (AC) to 2 x IEC-320-C13 (Device)
- 18AWG SJT, 10A, 125V
- UL Listed

System Requirements

- Computer or other devices with C14 power connectors

Package Includes

- 6-ft. AC Power Splitter Cable, 5-15P to 2 x C13

Description

Tripp Lite's P006-006-2, 6ft Universal AC Power Cord Splitter, allows you to connect two devices with C14 connections, such as computers, to one power outlet. Cuts down on cabling, as well as frees up space on UPS's, Surge Protectors, etc. Main trunk cable measures 47" from 5-15P plug to the splitter housing, 3" housing, and 22" each on the two C13 legs.

Features

- Power two computers or other device from one outlet
- Plug type - NEMA 5-15P (AC) to 2 x IEC-320-C13 (Device)
- 18AWG SJT, 10A, 125V
- 6ft overall length - 47" from 5-15P to split, 22" from split to C13's
- UL Listed

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Cable Length (m)	1.83
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA 5-15P
Connector B	IEC-320-C13 (X2)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.