

## Heavy-Duty Power Extension Cord, 20A, 12AWG (IEC-320-C19 to IEC-320-C20), 6-ft.

MODEL NUMBER: P036-006



### Highlights

- C19 to C20 Power Cord, 6ft
- 12AWG x 3C, 20 Amp Rated
- RoHS Compliant

### Package Includes

- C19 to C20 Power Cord, 6ft.

### Description

Use Tripp Lite's P036-006 in server applications that require a higher rated, heavier gauge cable. C19 to C20 connectors, 3 x 12ga conductors, 20A rated, 250V - ideal for use with Blade Server Chassis.

### Features

- Molded, Heavy-Duty Power Cord, 6ft.
- IEC-60320-C19 to IEC-60320-C20
- 12AWG x 3C, SJTW, 20A, 250Volt
- RoHS Compliant

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	6
Cable Length (m)	1.83



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	IEC-320-C20
Connector B	IEC-320-C19
Number of Connectors	2
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.