

# Heavy-Duty Power Extension Cord for PDU and UPS, 20A, 12AWG (IEC-320-C19 to NEMA L6-20P), 10-ft.

MODEL NUMBER: **P040-010**



### Highlights

- C19 to L6-20P power cord, 10 ft.
- 12AWG, SJT, 20A, 250V
- RoHS compliant

### Package Includes

- 10 ft. C19 to L6-20P Power Cord

### Description

Tripp Lite's Heavy Duty C19 to L6-20P 10 ft. power cord is constructed with 3 x 12AWG copper conductors, fully molded ends, and 250V/20A rating.

### Features

- Molded, Heavy-Duty Power Cord, 10 ft.
- IEC-320-C19 to NEMA L6-20P
- 12AWG, SJT, 20A, 250V
- RoHS compliant

## Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.05



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Connector A	NEMA L6-20P
Connector B	IEC-320-C19
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.