

Heavy-Duty Power Extension Cord for PDU and UPS, 20A, 12AWG (IEC-320-C19 to NEMA L6-20P), 14-ft.

MODEL NUMBER: **P040-014**



Highlights

- C19 to L6-20P power cord, 14 ft.
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Package Includes

- 14 ft. C19 to L6-20P Power Cord

Description

Tripp Lite's Heavy Duty C19 to L6-20P 14 ft. power cord is constructed with 3 x 12AWG copper conductors, fully molded ends, and 250V/20A rating.

Features

- Molded, Heavy-Duty Power Cord, 14 ft.
- IEC-320-C19 to NEMA L6-20P
- 12AWG, SJT, 20A, 250V
- RoHS compliant

Specifications

General Info	
RoHS	Y
OVERVIEW	
Style	Power Cables
Model Type	Power Cords
Cable Types	POWER
INPUT	
Cable Length (ft.)	14
Cable Length (m)	4.3



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA L6-20P
Connector B	IEC-320-C19
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.