



## Black Box Products

### Industrial > Cabling & Infrastructure

## Bulk Extended-Distance/Quiet Cable—Industrial Environment, PVC Jacket, 4 Conductors (2 Pairs), 500-ft. (152.4-m)

Send RS-232 data up to 500 feet in noisy environments.


EMN04A-0500

#### Further Details

Ideal for noisy environments where cable runs are next to power lines and other cabling systems that cause interference.

#### Product Highlights

- Low capacitance, braided foil shield.
- 24 AWG stranded construction.
- Guaranteed for life!



<b>Cable Type</b>	Twisted pair, PVC jacket
<b>Capacitance</b>	12 pF/ft. $\pm$ 2 pF/ft.
<b>Conductor Gauge</b>	24 AWG (7 x 32 AWG) stranded
<b>Resistance</b>	25 ohms/1000 ft.
<b>Shield</b>	One foil and one copper braid

NOTE: Technical specification weight is the unit weight. It is not the packaged shipping weight. For shipping weight, please contact Black Box customer service at 1-800-316-7107.