

MINIATURE LAMP (502) Details



Technical Specification

Part #	502				
Description	G4 1/2 M SCREW 5.1V .15A .6CP				
Bulb Shape	G-4 1/2	Filament	C-2R	Base Style	Miniature Screw (E10)
Glass Diameter (in)	0.55	MOL[†] (in)	1.06	LCL^{††} (in)	0.72
Glass Diameter (mm)	14	MOL (mm)	26.90	LCL (mm)	18.30
Volts	5.1	MSCP[‡]	0.6	Avg Life Hrs	100
Watts	0.765	Amps	0.15	RoHS Compliant	
E-Marked	No	Drawing		New Announcement	