

MINIATURE LAMP (1062) Details



Technical Specification

Part #	1062				
Description	RP11 DC BAY 40V .92A 50CP				
Bulb Shape	RP-11	Filament	C-5	Base Style	D.C. Bayonet (BA15d)
Glass Diameter (in)	1.38	MOL[†] (in)	2.25	LCL^{††} (in)	1.25
Glass Diameter (mm)	35	MOL (mm)	57.15	LCL (mm)	31.75
Volts	40	MSCP[‡]	50	Avg Life Hrs	100
Watts	36.8	Amps	0.92	RoHS Compliant	Yes
E-Marked	No	Drawing		New Announcement	