

T-1 3/4 Wedge Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
11	2.5	.200	.200	1,000	C-2R
111	2.7	.100	.230	5	S-2
56	5.0	.115	.150	20,000	C-2R
79	6.0	.200	.600	1,000	C-2R
16	6.3	.150	.340	5,000	C-2F
84	6.3	.040	.030	20,000	C-2R
86	6.3	.200	.400	20,000	C-2F
18	14.0	.040	.130	5,000	C-2F
37	14.0	.090	.500	1,500	C-2F
70	14.0	.150	1.50	100	C-2F
73	14.0	.080	.300	15,000	C-2F
74	14.0	.100	.700	500	C-2F
17	28.0	.065	.650	5,000	C-2F
85	28.0	.040	.300	7,000	C-2F

T-1 3/4 Midget Screw Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
8669	1.35	.060	.010	500	C-6
1767	2.50	.200	.200	500	C-2R
1769	2.50	.200	.200	500	C-2R
8693	2.70	.060	.040	6,000	C-2R
3153	5.00	.060	.150	5,000	C-2R
342	6.00	.040	.030	10,000	C-2V
1768	6.00	.200	.600	1,000	C-2R
7323	6.00	.200	.550	5,000	C-2R
378	6.30	.200	.400	20,000	C-2F
1775	6.30	.075	.230	1,000	C-2R
389	10.0	.040	.080	5,000	C-2F
373	14.0	.080	.500	1,500	C-2F
383	14.0	.080	.500	750	C-2F
8162	14.0	.100	.500	10,000	C-2F
8362	14.0	.080	.300	15,000	C-2F
8536	18.0	.040	.150	10,000	C-2F
335	28.0	.040	.340	4,000	C-2F
335LSV	28.0	.060	.340	25,000	C-2F
369	28.0	.040	.340	4,000	C-2F
399	28.0	.040	.300	7,000	C-2F
8369	28.0	.065	.650	15,000	C-2F
8384	28.0	.040	.150	10,000	C-2F