

Item #	Description	1-9	10-24	25-99	100-249	250-499
--------	-------------	-----	-------	-------	---------	---------

RoHS 195-Series 50 Ohm Coaxial Pigtails

195 Series

50 Ohm Impedance

195R Series Low-Loss Cable

- Center Conductor: Solid bare copper
- Shielding: Foil + tinned copper braid (90% coverage)
- Insulation: Physical foam polyethylene (PTFE for Plenum Rated)
- Jacket: Polyvinyl Chloride (CMP Grade for Plenum Rated)
- Operating Temperature: -20°C - +60°C

NOMINAL ATTENUATION		
MHz	db/100 ft	db/100m
900	11.1	36.5
1800	16.0	52.5
2500	19.0	62.4
5800	29.9	98.1

CA-RBPNFA002	195-Series Pigtails, Reverse Polarity BNC Plug / Type N Female Bulkhead, 2.0 ft	18.95	17.05	15.16	13.26	11.37
CA-RBPNFA002	195-Series Pigtails, Reverse Polarity BNC Plug / Type N Female, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-RBPNMA002	195-Series Pigtails, Reverse Polarity BNC Plug / Type N Male, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-RSJRTPB010	195-Series Pigtails, Reverse Polarity SMA Jack / Reverse Polarity TNC Plug, 10.0 ft	19.99	17.99	15.99	13.99	11.99
CA-RSJRTPB020	195-Series Pigtails, Reverse Polarity SMA Jack / Reverse Polarity TNC Plug, 20.0 ft	24.99	22.49	19.99	17.49	14.99
CA-RSPNFA002	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Female Bulkhead, 2.0 ft	19.00	17.10	15.20	13.30	11.40
CA-RSPNFA002	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Female, 2.0 ft	15.00	13.50	12.00	10.50	9.00
CA-RSPNMA002	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Male, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-RSPNMA004	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Male, 4.0 ft	22.00	19.80	17.60	15.40	13.20
CA-RSPNMB001	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Male, 1.0 ft	10.99	9.89	8.79	7.69	CALL
CA-RSPNMA010	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Male, 10.0 ft	25.00	22.50	20.00	17.50	15.00
CA-RSPNMA020	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Male, 20.0 ft	27.00	24.30	21.60	18.90	16.20
CA-RSPRNPAA002	195-Series Pigtails, Reverse Polarity SMA Plug / Reverse Polarity Type N Plug, 2.0 ft	29.99	26.99	23.99	20.99	17.99
CA-RSPRPSJA010	195-Series Pigtails, Reverse Polarity SMA Plug / Reverse Polarity SMA Jack, 10.0 ft	25.00	22.50	20.00	17.50	15.00
CA-RSPRPSJA020	195-Series Pigtails, Reverse Polarity SMA Plug / Reverse Polarity SMA Jack, 20.0 ft	27.00	24.30	21.60	18.90	16.20
CA-RSPRTPAA002	195-Series Pigtails, Reverse Polarity SMA Plug / Reverse Polarity TNC Plug, 2.0 ft	19.99	17.99	15.99	13.99	11.99
CA-RTPNFBAA002	195-Series Pigtails, Reverse Polarity SMA Plug / Type N Female Bulkhead, 2.0 ft	19.00	17.10	15.20	13.30	11.40
CA-RTPNFBAA004	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Female Bulkhead, 4.0 ft	20.00	18.00	16.00	14.00	12.00
CA-RTPNFA002	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Female, 2.0 ft	15.00	13.50	12.00	10.50	9.00
CA-RTPNFA004	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Female, 4.0 ft	16.00	14.40	12.80	11.20	9.60
CA-RTPNFA010	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Female, 10.0 ft	19.00	18.24	17.48	16.15	14.25
CA-RTPNMA002	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Male, 2.0 ft	9.99	8.99	7.99	6.99	5.99
CA-RTPNMA004	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Male, 4.0 ft	12.99	11.69	10.39	9.09	7.79
CA-RTPNMA010	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Male, 10.0 ft	14.99	13.49	11.99	10.49	8.99
CA-RTPNMA020	195-Series Pigtails, Reverse Polarity TNC Plug / Type N Male, 20.0 ft	17.99	16.19	14.39	12.59	10.79
CA-RTPRTJBA002	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack BH, 2.0 ft	18.99	17.09	15.19	13.29	11.39
CA-RTPRTJA002	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack, 2.0 ft	13.00	11.70	10.40	9.10	7.80
CA-RTPRTJA004	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack, 4.0 ft	22.00	19.80	17.60	15.40	13.20
CA-RTPRTJA010	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack, 10.0 ft	17.00	15.30	13.60	11.90	10.20
CA-RTPRTJA020	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Jack, 20.0 ft	22.00	19.80	17.60	15.40	13.20
CA-RTPRTPAA002	195-Series Pigtails, Reverse Polarity TNC Plug / Reverse Polarity TNC Plug, 2.0 ft	18.99	17.09	15.19	13.29	11.39
CA-RTPRNMA002	195-Series Pigtails, Reverse Polarity TNC Right Angle Plug / Type N Male, 2.0 ft	14.99	13.79	12.59	11.39	10.19
CA-RTPRNMA002	195-Series Pigtails, Reverse Polarity TNC Rt. Angle Plug / Type N Male, Rt. Angle, 2.0 ft	14.99	13.79	12.59	11.39	10.19
CA-RTPRNMA004	195-Series Pigtails, Reverse Polarity TNC Right Angle Plug / Type N Male, 4.0 ft	22.00	19.80	17.60	15.40	13.20
CA-RTPRNMA010	195-Series Pigtails, Reverse Polarity TNC Right Angle Plug / Type N Male, 10.0 ft	25.00	22.50	20.00	17.50	15.00
CA-RTPRNMA020	195-Series Pigtails, Reverse Polarity TNC Right Angle Plug / Type N Male, 20.0 ft	27.00	24.30	21.60	18.90	16.20
CA-SSMNFAN06	195-Series Pigtails, Shrouded SMA / Type N Female, 6 in	10.49	9.44	8.39	7.34	CALL
CA-SSMNFAN06	195-Series Pigtails, Shrouded SMA / Type N Male, 6 in	10.49	9.44	8.39	7.34	CALL
CA-SSMNFMA002	195-Series Pigtails, Shrouded SMA / Type N Male, 2.0 ft	11.99	11.03	10.07	9.11	8.15
CA-SMNFBAA002	195-Series Pigtails, SMA Male / Type N Female Bulkhead, 2.0 ft	18.99	17.09	15.19	13.29	11.39
CA-SMNFA002	195-Series Pigtails, SMA Male / Type N Female, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-SMNFA004	195-Series Pigtails, SMA Male / Type N Female, 4.0 ft	18.99	17.09	15.19	13.29	11.39
CA-SMNMA002	195-Series Pigtails, SMA Male / Type N Male, 2.0 ft	15.00	13.50	12.00	10.50	9.00
CA-SMNMA004	195-Series Pigtails, SMA Male / Type N Male, 4.0 ft	16.00	14.40	12.80	11.20	9.60
CA-SMNMA010	195-Series Pigtails, SMA Male / Type N Male, 10.0 ft	19.00	17.10	15.20	13.30	11.40
CA-SMRNFBA002	195-Series Pigtails, SMA Right Angle Male / Type N Female Bulkhead, 2.0 ft	18.99	17.09	15.19	13.29	11.39
CA-SMRNFMA002	195-Series Pigtails, SMA Right Angle Male / Type N Female, 2.0 ft	14.99	13.79	12.59	11.39	10.19
CA-SMRNFMA002	195-Series Pigtails, SMA Right Angle Male / Type N Male, 2.0 ft	14.99	13.79	12.59	11.39	10.19
CA-TMNFMA002	195-Series Pigtails, TNC Male / Type N Female, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-TMNFMA002	195-Series Pigtails, TNC Male / Type N Male, 2.0 ft	14.99	13.49	11.99	10.49	8.99
CA-WMNFMA002	195-Series Pigtails, WaveRider / Type N Female, 2.0 ft	15.99	14.71	13.43	12.15	10.87
CA-WMNFMA002	195-Series Pigtails, WaveRider / Type N Male, 2.0 ft	15.99	14.71	13.43	12.15	10.87
CA-WMNFMA005	195-Series Pigtails, WaveRider / Type N Male, 5.0 ft	16.99	15.63	14.27	12.91	11.55

LOW-LOSS CABLES

Did you know...
These cables have excellent low loss characteristics and are RoHS compliant.

Tip *Some cables are called coaxial, a term derived from the construction of the cable*

In a coaxial cable electrical impulse signal is transmitted along the cable length between the center conductor and the outer conductor. The center conductor and the outer conductor share the same center line or axis hence the term coaxial.

Cable Construction Cross Section

Center Conductor Outer Conductor

To see our entire product offering go to... www.L-com.com

