

SmartRack 18U Heavy-Duty Side-Mount Wall-Mount Rack Enclosure Cabinet

MODEL NUMBER: **SRW18UHD**



Highlights

- Only protrudes off the wall 24"
- Full mounted equipment access front, rear and side
- Multiple mounting positions for optional fans([SRFANWM](#))
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Package Includes

- SRW18UHD Wall-mount enclosure cabinet
- (42) M6 cage nuts
- (42) M6 equipment mounting screws
- (42) M6 washers
- (42) 12-24 equipment mounting screws
- (1) Key set
- Owner's Manual

Description

The SRW18UHD is a wall-mount, rack enclosure that can accommodate full server depth equipment (29"-31") but only protrudes off the wall 24". Since the equipment is mounted in the wall cabinet sideways, the leverage off the wall is less and the weight capacity is increased greatly. Access to mounted equipment is still great due to full access doors on each side of the cabinet (for front and rear equipment access) and one full removable side panel for access along the length of the mounted equipment. Adjustable front and rear mounting rails have square holes (default position) and tapped holes to accommodate 18U of equipment.

Features

- Heavy-Duty/High Weight Capacity side-mount construction
- 18U of server depth equipment capacity
- Fully vented doors and side panel
- Adjustable front and rear rails
- Dual-rail mounting designs supports equipment mounting via square holes or threaded holes
- 500lb weight capacity

Specifications

OVERVIEW	
Application	Where full server depth equipment is mounted but deep (33" depth) cabinets protruding into the room can't be permitted. Rated to hold 18U of full depth servers (high weight capacity).
PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	32.5



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Installed Whole System Maximum Rack Depth (cm)	82.6
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	18
Shipping Dimensions (hwd / in.)	41.33 x 37.8 x 25.6
Shipping Dimensions (hwd / cm)	104.9 x 96 x 65
Shipping Weight (lbs.)	137.5
Shipping Weight (kg)	62.36
Unit Dimensions (hwd / in.)	36.96 x 36.22 x 24.77
Unit Dimensions (hwd / cm)	93.88 x 92 x 62.92
Unit Weight (lbs.)	119.9
Unit Weight (kg)	54.38
Unit Dimensions (cm)	93.87 x 92 x 62.9
Color	Black
Weight Capacity - Stationary (lbs.)	500
EIA Mounting Rails	Square holes / 12-24 threaded holes
Weight Capacity - Stationary (kg)	181.4
Hinged (Swings Away from Wall Bracket)	No
SPECIAL FEATURES	
Seismic Rack	No
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>