

TAA-Compliant Protect It! 3-Outlet Surge Protector, Direct Plug-In, 540 Joules, 2.1A USB Charger

MODEL NUMBER: SK120USBTAA



Description

The SK120USBTAA surge suppressor offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability with fold down plug and carrying pouch and features 3 outlets, 1 in front and 1 on each side of unit and 540 joules of surge energy absorption. The diagnostic LED alerts you to potential wiring or protection faults before connected equipment is damaged. 2.1 amp USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- Compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases
- 3 outlets / direct plug-in - 1 on face of product and 1 on each side
- Surge suppression rating: 540 joules
- 2.1 amp USB Charger
- Fold down plug
- Carrying pouch
- EMI/RFI noise filtering
- Diagnostic LED indicates Protected (green)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Highlights

- Compliant with the Federal Trade Agreement Act (TAA) for GSA schedule purchases
- 3 outlets/direct plug-in
- 540 joule rating
- 2.1 amp USB charging
- Fold down plug
- Carrying pouch
- Diagnostic LED
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection
- Dual port USB charging ports for smartphones, tablets, MP3 Players and other portable devices

Package Includes

- SK120USBTAA surge suppressor
- Carrying pouch

Specifications

OUTPUT	
Charging Ports / Amps	(2) 2.1A
Frequency Compatibility	60 Hz



Output Receptacles	(3) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Outlet Type	NEMA 5-15R
USB Charging	Yes
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Length (m)	0.00
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	540
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	500
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
Immunity	Conforms to IEE 587/ANSI C62.41
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	4.29 x 2.24 x 1.38
Unit Dimensions (hwd / cm)	10.9 x 5.69 x 3.51
Unit Weight (lbs.)	.31
Unit Weight (kg)	.14
Material of Construction	Plastic



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black
Receptacle Color	Black
Metal Case	No
SPECIAL FEATURES	
Right-Angle Plug	No
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>