

Universal Computer Power Cord, 10A, 18AWG (NEMA 5-15P to Right Angle IEC-320-C13), 14-ft.

MODEL NUMBER: P006-014-13RA



Highlights

- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device) Right Angle
- 18AWG (0.824mm²), SJT, 10A, 125V
- UL Listed

Package Includes

- 14-ft. Universal AC Power Replacement Cord, NEMA 5-15P Plug to IEC-320-C13 Receptacle, Right Angle Exit

Description

Tripp Lite's line of AC power cords offer PC users a solution to their power connectivity problems. This 14-ft cable will replace the power cable on most computers and peripherals that have a removable power cord. Cable features an AC style plug (NEMA 5-15P) on one end and a computer style receptacle (IEC-320-C13) on the other end. Right Angle exit allows room for the power cable in tight situations, such as against a wall. UL Listed.

Features

- C13 Right Angle exit ideal for tight spaces
- 14-ft. replacement power cable for a PC, printer, monitor or any other device with like plugs
- Universal design
- Plug type - NEMA 5-15P (AC) to IEC-320-C13 (Device) Right Angle
- 18AWG (0.824mm²), SJT, 10A, 125V
- UL Listed

Specifications

INPUT	
Cable Length (ft.)	14
Cable Length (m)	4.27
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	NEMA 5-15P



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connector B	IEC-320-C13 - RIGHT ANGLE
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>