

Heavy-Duty Power Cord, 20A, 12AWG (IEC-320-C19 to NEMA L6-30P), 12-ft.

MODEL NUMBER: P040-012-P30



Highlights

- C19 to L6-30P Power Cable, 12-ft.
- 12 AWG x 3C
- RoHS Compliant

Package Includes

- C19 to L6-30P Power Cord, 12-ft.

Description

Tripp Lite Heavy-Duty C19 to L6-30P 12-ft. Power Cord. Constructed with 3 x 12 AWG copper conductors, fully molded ends, 100-250V/20A rating.

Features

- Molded, Heavy-Duty Power Cable, 12-ft.
- IEC-60320-C19 to NEMA L6-30P
- 12 AWG x 3C, SJT, 20A, 100-250V
- RoHS Compliant

Specifications

INPUT	
Cable Length (ft.)	12
Cable Length (m)	3.7
PHYSICAL	
Color	Black
CONNECTIONS	
Connector A	IEC-320-C19
Connector B	NEMA L6-30P
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>