

Universal Reversible USB 2.0 Hi-Speed Cable (Reversible A to Left-angle 5Pin Micro B M/M), 3-ft.

MODEL NUMBER: UR050-003-LAB



Description

Tripp Lite UR050-003-LAB, 3-ft. USB 2.0 A to Left-Angle Micro-B cable, features a Universal / Reversible "A" connector, which takes the guesswork out of which way to position the "A" connector for plugging. Furthermore, the Left-Angle Micro B connector is ideal for situations where space is at a premium, and reduces stress / excessive bending on the cable. Micro-USB is the next generation of USB connector that will be found on Cell Phones, PDA's, USB On-the-Go (OTG) devices, Digital Cameras, and more. Smaller and more durable (10,000 insertion cycles) than the existing mini-B connectors, the Micro-USB will also handle Power transfers, as well as Data. The USB Implementers Forum (USB-IF) has designed the Micro-USB to eliminate many of the proprietary Mini connectors found on different manufacturers digital devices, and it will be the standard USB connection on phones from the major cell phone manufacturers. USB 2.0 rated cable handles 480Mbps data transfer rates.

Features

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Left-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Available in lengths up to 10-ft.
- 480Mbps USB 2.0 Data Transfer Rates
- Data and Power transference

Specifications

OVERVIEW	
Cable Type	USB
OUTPUT	
USB Charging	No

Highlights

- Universal / Reversible A connector eliminates guess-work as to connector orientation
- Left-Angle Micro B connector ideal in situations where space is at a premium, and reduces stress / excessive bending on the cable
- Next Generation USB Digital Device Connector
- Provides both Data and Power transfers
- USB 2.0 480Mbps Transfer rates

System Requirements

- Digital devices that use the USB Micro-B Female socket

Package Includes

- 3-ft. USB2.0 Universal / Reversible A to Left-Angle Micro-USB B Device Cable (A Male to Micro-B Male)



INPUT	
Cable Length (ft.)	3
Cable Length (m)	0.91
PHYSICAL	
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	-10/+75° C (14 to 167° F)
Storage Temperature Range	-20/+80° C (-4 to 176° F)
CONNECTIONS	
Connector A	REVERSIBLE USB A (MALE)
Connector B	MICRO-USB B (MALE)
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>