

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

## MTP/MPO Patch Cable, 12 Fiber, 40GbE, 40GBASE-SR4, OM3 Plenum-Rated - Aqua, 5M (16-ft.)

MODEL NUMBER: **N844-05M-12-P**



### Highlights

- Hi-density MTP/MPO 12-fiber connectors for reduced cabling
- Push/Pull tab connectors offer maximum accessibility in high density installations; install / remove with one hand
- OM3 rated 50/125 Multimode
- Supports to 40GbE speeds

### Applications

- Hi-density fiber patching between data center MDF and IDF

### Package Includes

- 5 Meter MTP / MPO Patch Cable, 12 Fiber, 40GbE Aqua OM3 Plenum

### Description

Tripp Lite MTP/MPO to MTP/MPO fiber patch cables allow high-density connections between network equipment in telecommunication rooms. They feature Push/Pull tab connectors that offer maximum accessibility in high density installations; install / remove with one hand. The MTP/MPO connector is approximately the same size of a SC connector but since it can accommodate 12 fibers, it provides up to 12 times the density, thereby offering savings in circuit card and rack space. N844 series cables are manufactured using laser-optimized, 50/125, OM3 multimode cable, and support speeds up to 40GbE.

### Features

- MTP / MPO Push-Pull Connectors for Quick Fiber Optic connections
- Push/Pull tab connectors offer maximum accessibility in high density installations; install / remove with one hand
- 12 times the density of SC style connectors
- No need for long fan-out cables or individual long duplex cable runs
- High Density design cuts down on installation costs
- 50/125 OM3 Rated Multimode Fiber, 850nm
- Plenum rated jacket
- Unique cable ID label for Quality Control and Traceability
- Each cable 100% tested for low insertion loss and back reflection
- Test data supplied with each cable
- Custom lengths available

## Specifications

| OVERVIEW   |              |
|------------|--------------|
| Fiber Type | 50/125 - OM3 |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.triplite.com

|                                     |                           |
|-------------------------------------|---------------------------|
| Cable Type                          | Multimode; 10G/40G/100G   |
| <b>INPUT</b>                        |                           |
| Cable Length (ft.)                  | 16                        |
| Cable Length (m)                    | 5                         |
| <b>PHYSICAL</b>                     |                           |
| Color                               | Aqua                      |
| <b>COMMUNICATIONS</b>               |                           |
| Network Speed                       | 10Gbps / 40Gbps / 100Gbps |
| <b>CONNECTIONS</b>                  |                           |
| Connector A                         | MTP                       |
| Connector B                         | MTP                       |
| <b>WARRANTY</b>                     |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.triplite.com/products/product-certification-agencies>