

OM3 can support 40GBASE-SR4 / 100GBASE-SR10 in applicable parallel optics networks

MTP/MPO Fan-Out Cable, MTP/MPO to 8xLC, 40GbE, 40GBASE-SR4, OM3 Plenum-Rated - Aqua, 5M (16-ft.)

MODEL NUMBER: **N844-05M-8LC-P**



Highlights

- MTP / MPO to 8 x LC Fan-out Cable
- OM3, 40GbE rated, 40GBASE-SR4
- 50/125 Multimode

Applications

- Used with 40GBASE-SR4 networking hardware

Package Includes

- 5M (16-ft.) MTP / MPO Fan-out Cable, MTP/MPO to 8 x LC, 40GbE OM3 Plenum

Description

Tripp Lite's MPO/MTP Multi-Fiber cabling system is ideally suited for a high density environment that demands space saving and reduced cable management solutions. MPO/MTP fan-outs support various connections from multi-fiber to single-fiber out. N844-xxM-8LC-P cables utilize 8 fibers to fully transmit 40GBASE-SR, 4 fibers in each direction transmitting 10Gb each.

Features

- MTP / MPO to 8 x LC, 5 Meter Fan-out Cable
- 40GbE rated OM3 50/125 Multimode
- Plenum rated jacket

Specifications

OVERVIEW	
Fiber Type	50/125 - OM3
Cable Type	Multimode; 10G/40G/100G
INPUT	
Cable Length (ft.)	16
Cable Length (m)	5
PHYSICAL	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Color	Aqua
COMMUNICATIONS	
Network Speed	10Gbps / 40Gbps / 100Gbps
CONNECTIONS	
Connector A	MTP
Connector B	LC (X8)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>