

## Hole Grommet

14.78.748

Product No. **14.78.748**

Type	Grommets
Model	Diaphragm Inside
Design	groove revolving
Inside Dia.	48.00 mm
Mounting Hole Dia.	60.00 mm
Max. Panel Thickness	2.50 mm
Color	Black
Material	Polypropylene / Neoprene
Special Features	Temperature Range: -30°C to +90°C
Thickness-H	10.00 mm
Reach/SVHC free	yes

