


PRODUCT SPECIFICATION

**Carl
Kammerling**
International

Brand	C.K
Product Range	Hacksaws
Catalogue number	814, 903, 905, 834, 836A and 837
Date	11/10/2012

<p>Range Description Professional quality Hacksaws and Junior Hacksaws</p>	
<p>Features</p> <p>814</p> <ul style="list-style-type: none"> • Heavy duty hacksaw with comfortable rubber grips • Quick release blade mechanism for convenience • Blade tension adjuster • 45 and 90 degree blade positions for versatility • Spare blade storage in back frame for convenience • Supplied complete with top quality cekaflex HHS bi-metal 24 tpi blade • Display packed <p>903</p> <ul style="list-style-type: none"> • Heavy duty hacksaw with Aluminium handle and strong box section steel beam for professional performance • Integral blade tension lever • Blade adjustable through 360 degrees at 45 degree intervals • Supplied complete with top quality cekaflex HHS bi-metal 24 tpi blade • Sold loose <p>905</p> <ul style="list-style-type: none"> • Heavy duty hacksaw with Aluminium handle and strong box section steel beam for professional performance • Easy blade fitting and tensioning for convenience • 45 and 90 degree blade positions for versatility • Spare blade storage in back frame for convenience • Supplied complete with top quality cekaflex HHS bi-metal 24 tpi blade • Display packed <p>834</p> <ul style="list-style-type: none"> • High quality tensioned steel frame • Epoxy coated for protection • Non protruding blade fixing – avoids injury in use • 1 x 150mm 32 tpi high quality blade fitted and 1 spare supplied • Display packed 	

836A/837

- Aluminium frame – strong and lightweight
- Fast easy blade fitting with screw tensioning for convenience
- Blade adjustable to 6 angles for maximum flexibility
- Lightweight mitre box – with three cutting angles and extended lip for stable positioning (837 only)
- 24 TPI Blade
- Display packed



836A



837

Item Number	Item Description	EAN No	Commodity code	Shelf box Qty
T0814	Quick change hacksaw 300mm	5013969023756	82021000	3
T0903 12	Hacksaw 300mm	5013969412901	82021000	N/A
T0905	Hacksaw 300mm	5013969019384	82021000	3
T0834	Junior hacksaw	5013969408706	82021000	6
T0836A	Mini hacksaw	5013969019247	82021000	6
T0837	Mini hacksaw and mitre box	5013969062816	82021000	5
T0932 12	Hacksaw Blade 12" x 18TPI (Pack of 25)	5013969409918	82021000	10
T0933 12	Hacksaw Blade 12" x 24TPI (Pack of 25)	5013969409925	82029100	10
T0934 12	Hacksaw Blade 12" x 32TPI (Pack of 25)	5013969409932	82029100	10
T0931R 12	Pack of three T0933R 12 Hacksaw Blades	5013969409703	82029100	12
T0932R 1218	Pack of three T0932R 12 Hacksaw Blades	5013969409949	82029100	12
T0934R 1232	Pack of three T0934R 12 Hacksaw Blades	5013969409956	82029100	12
T0835	Pack of ten Junior hacksaw blades 32 tpi	5013969408805	82029100	1

Technical product information	
Standards compliance	None applicable
User health and safety information	Users are advised to wear safety goggles
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	Not applicable
Warranty	C.K tools are guaranteed for life against imperfect materials or workmanship

	Damage caused through inappropriate use is not covered
Country of origin	T0814 – Taiwan T0903 12 – Italy T0905 – Taiwan T0834 – Taiwan T0836A - Taiwan T0837 – Taiwan T0932 12 – India T0933 12 – India T0934 12 – India T0931R 12 – India T0932R 1218 – India T0934R 1232 - India T0835 – Germany

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T0814	160	35	420	979	160	40	470	1044
T0903 12	130	20	440	545				
T0905	145	25	400	550	145	32	440	584
T0834	62	6	245	113	85	9	255	127
T0836A	90	20	260	112	130	25	315	156
T0837	78	22	258	166	157	35	320	225
T0932 12	12	1	310	17	30	15	360	438
T0933 12	12	1	310	17	30	15	360	438
T0934 12	12	1	310	17	30	15	360	438
T0931R 12	12	1	310	17	63	2	370	68
T0932R 1218	12	1	310	17	63	2	370	68
T0934R 1232	12	1	310	17	63	2	370	68
T0835	150	5	6	2	40	12	188	30

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g Inc product	No of cartons on base	Number of rows high
T0814	175	450	95	3310		
T0903 12						
T0905	175	450	95	1979		

T0834	95	275	55	837		
T0836A	150	335	115	1036		
T0837	165	333	135	1244		
T0932 12	165	340	40	4418		
T0933 12	165	340	40	4418		
T0934 12	165	340	40	4418		
T0931R 12	67	395	50	874		
T0932R 1218	67	395	50	874		
T0934R 1232	67	395	50	874		
T0835						

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T0814			55	Backing card	10	Bag	178	Box
T0903 12								
T0905			34	Backing card	10	Bag	227	Box
T0834			13	Backing card			113	Box
T0836A	16	Blister	30	Backing card			100	Box
T0837	23	Blister	36	Backing card			119	Box
T0932 12			13	Box	38	Box		
T0933 12			13	Box	38	Box		
T0934 12			13	Box	38	Box		
T0931R 12	17	Wallet					58	Box
T0932R 1218	17	Wallet					58	Box
T0934R 1232	17	Wallet					58	Box
T0835			10	Box				