

Capacitor, film, 0.22 uF, +/-10% Tol, General Purpose, 400 VDC@85C



Note: '()' correspond to the letters used in the product bulletin

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	16.5	+/-0.2
W	15	+/-0.2
T	7	+/-0.2
F	0.5	NOM

Packaging Specifications	
Package Kind:	T&R
Package Size:	Standard
Package Quantity:	500

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polyester (Stacked)
Application:	General Purpose
Style:	Surface Mount
Chip Size:	6560
RoHS:	Yes

Specifications	
Capacitance:	0.22 uF
Voltage:	400 VDC
Tolerance:	+/-10%
Voltage AC:	200 VAC
Rated Temperature:	85C
Temperature Range:	-55/+125C
Dissipation Factor @ 1 kHz:	0.8%
Dissipation Factor @ 10 kHz:	1.2%
Dissipation Factor @ 100kHz:	3%
Insulation Resistance:	1 GOhm
Maximum dVdT:	20 v/us