UNIVERSAL ENCLOSURES

Plastic Flanged Cases

Multi-purpose flanged enclosure designed for wall-mounting or surface mount devices.

- Suitable for measuring instruments, communication device, controller etc.
- Lid and base moulded in flame resistant ABS.
- Lid mounted by four M3 machine screws.
- Excellent properties for machining.
- Available in 18 sizes in white & dark grey, UL94-V0.

SPECIFICATION	
Materials	Lid & base high impact ABS- UL94-V0
Operating temperature	-10°C to +60°C
Standard colours	Off white & dark grey
Standard unit includes:	Lid and Base, Nickel plated screw



Dark Grey Enclosure

SIZE	MANUFACTURER	LENGTH	WIDTH	HEIGHT
	PART NO.			
1	TWF4-2-5D	50mm	35.4mm	22mm
7	TWF5-3-9D	90mm	45.6mm	27.5mm
8	TWF7-2-11D	105mm	70.6mm	20.5mm
9	TWF7-4-11D	105mm	70.6mm	35.5mm
10	TWF7-5-11D	105mm	70.6mm	50.5mm
11	TWF7-3-13D	130mm	65.5mm	25.5mm
12	TWF7-5-13D	130mm	65.5mm	50mm
13	TWF8-2-8D	80mm	80.6mm	23.5mm
14	TWF8-4-8D	80mm	80.6mm	43.5mm
15	TWF9-4-17D	170mm	86mm	35mm
16	TWF9-6-17D	170mm	86mm	60mm
17	TWF11-5-22D	220mm	110.3mm	45mm
18	TWF11-8-22D	220mm	110.3mm	75mm
19	TWF13-3-13D	125mm	125.6mm	25mm
20	TWF13-5-13D	125mm	125.6mm	45mm
21	TWF13-3-18D	175mm	125.6mm	25mm
22	TWF13-5-18D	175mm	125.6mm	45mm
23	TWF13-7-18D	175mm	125.6mm	65mm

^{*} length includes flange

Off-white Enclosure

SIZE	MANUFACTURER	LENGTH	WIDTH	HEIGHT
	PART NO.			
1	TWF4-2-5W	50mm	35.4mm	22mm
7	TWF5-3-9W	90mm	45.6mm	27.5mm
8	TWF7-2-11W	105mm	70.6mm	20.5mm
9	TWF7-4-11W	105mm	70.6mm	35.5mm
10	TWF7-5-11W	105mm	70.6mm	50.5mm
11	TWF7-3-13W	130mm	65.5mm	25.5mm
12	TWF7-5-13W	130mm	65.5mm	50mm
13	TWF8-2-8W	80mm	80.6mm	23.5mm
14	TWF8-4-8W	80mm	80.6mm	43.5mm
15	TWF9-4-17W	170mm	86mm	35mm
16	TWF9-6-17W	170mm	86mm	60mm
17	TWF11-5-22W	220mm	110.3mm	45mm
18	TWF11-8-22W	220mm	110.3mm	75mm
19	TWF13-3-13W	125mm	125.6mm	25mm
20	TWF13-5-13W	125mm	125.6mm	45mm
21	TWF13-3-18W	175mm	125.6mm	25mm
22	TWF13-5-18W	175mm	125.6mm	45mm
23	TWF13-7-18W	175mm	125.6mm	65mm

^{*} length includes flange