

AMD APU A10 7800 FM2+ RETAIL



Manufacturer: AMD

Product Name: AMD APU A10 7800 Retail - (FM2+/Quad Core/3.50GHz/4MB/65W)

Model Number: AD7800YBJABOX

Package Type: Retail

Warranty: 3 Years

Interface: Socket FM2+

No. of Cores: 4

Threads: 4

Core Frequency: 3.50GHz

Core Turbo Frequency (Max): 3.90GHz

Process Technology: 28nm

Thermal Design Power: 65W

Memory Types: DDR3 2133 (Max.)

Memory Channel: Dual

Integrated Graphics: AMD Radeon R7

L1 Cache: 2 x 96 KB 3-way set associative shared instruction caches
4 x 16 KB 4-way set associative data caches

L2 Cache: 4MB

Package Width: 8.5cm

Package Length: 11.5cm

Package Height: 6cm

Gross Weight: 0.26Kg

Special Features:

- Trailing Bit Manipulation instructions
- AMD 64-bit technology
- Virtualization technology
- Enhanced Virus Protection
- Turbo Core 3.0 technology

Package Contents: APU, Heatsink and Fan

Royal Mail Compliance: Large Box