



## Main

Range	Thalassa TBP
Device application	Multi-purpose
Category	Industrial box
Height	192 mm
Width	121 mm
Depth	87 mm
Internal height	175 mm
Internal width	105 mm
Internal depth	80 mm
Enclosure mounting	Wall mounted
Device composition	4 x cover screw 1 x cover 1 x body
Quantity per set	Set of 2
Body type	One piece moulded
Type of front cover	Low plain cover
Cover fixing	Plastic screws
Lock type	Outside sealed area: flat screwdriver captive screw
Removable parts	Cover, by captive screws

## Complementary

Material	Polycarbonate
Colour	Grey ( RAL 7035 )
Standards	IEC 62208 UL 508 A
Product certifications	DEMKO SEMKO TÜV UL
IP degree of protection	IP66conforming to NEMA 4.4X
IK degree of protection	IK08conforming to IEC 62262
Fire resistance	960 °C
Ambient air temperature for storage	-15...60 °C
Operating temperature	-25...80 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0940 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.