

HOME



SEARCH



LOCATE DEALER



LOG ON



CONTACT US



platt

## FOAM-FILLED CASES



## Blow Molded Cases

ZOOM

Meet Platt's low cost solution to "Make-Your-Own" case needs.

These cases are manufactured from prime, high-density polyethylene, with double wall construction. The textured exteriors resist dents, cracking and scuffs. The shells are unaffected by extreme temperatures.

The hardware features mechanical latches that are field replaceable, and a mechanical hinge system that is made to last.

All cases meet U.S. 94B Specifications as an electrical insulator and are impervious to chemical attack.

Platt Part #	Inside Dim. (L)	Inside Dim. (W)	Inside Dim. (D)	Outside Dim. (L)	Outside Dim. (W)	Outside Dim. (D)
102	5.625	3.625	1.375	6.5	4.5	1.688
103	5.625	3.625	1.875	6.5	4.5	2.125
104	7.125	4	1.438	8	5	1.75
105	7.125	4	1.938	8	5	2.125
106	7.5	5	1.688	8.5	6	2
107	7.5	5	2.188	8.5	6	2.5
108	7.5	5	2.688	8.5	6	3
202	8.5	5.5	1.688	9.5	6.5	2
203	8.5	5.5	2.688	9.5	6.5	2.5
204	8.5	5.5	2.688	9.5	6.5	3
205	8.5	5.5	3.188	9.5	6.5	3.5



<b>206</b>	9.5	6	1.938	10.5	7	2.25
<b>207</b>	9.5	6	2.688	10.5	7	3
<b>208</b>	9.5	6	3.438	9.5	7	3.75
<b>302</b>	10.188	6.5	1.938	11.313	7.5	2.25
<b>303</b>	10.188	6.5	2.688	11.313	7.5	3
<b>304</b>	10.188	6.5	3.438	11.313	7.5	3.75
<b>305</b>	11	7	1.938	12	8	2.25
<b>306</b>	11.5	7	2.688	12	8	3
<b>307</b>	11	7	3.438	12	8	3.75
<b>308</b>	12.375	6.875	2.875	13.5	8	3.25
<b>309</b>	12.375	6.875	4.063	13.5	8	4.375
<b>310</b>	12.375	6.875	5.188	13.5	8	5.5
<b>402</b>	12.375	7.875	2.875	13.5	9	3.25
<b>403</b>	12.375	7.875	4	13.5	9	4.375
<b>404</b>	12.375	7.875	5.125	13.5	9	5.5
<b>405</b>	12.375	5.875	2.875	13.5	10	3.25
<b>406</b>	12.4	8.9	4	13.5	10	4.375
<b>407</b>	12.375	8.875	5.125	13.5	10	5.5
<b>503</b>	13.875	8.875	2.875	15	10	3.25
<b>504</b>	13.875	8.875	4	15	10	4.375
<b>505</b>	13.875	8.875	5.125	15	10	5.5
<b>506</b>	13.875	9.875	2.875	15	11	3.25
<b>507</b>	13.875	9.875	4	15	11	4.375
<b>508</b>	13.875	9.875	5.125	15	11	5.5
<b>604</b>	14.875	10.375	2.875	16	11.5	3.25

<b>605</b>	14.875	10.375	4	16	11.5	4.375
<b>606</b>	14.875	10.375	5.125	16	11.5	5.5
<b>607</b>	15.875	10.875	2.875	17	12	3.125
<b>608</b>	15.875	10.875	2.875	17	12	4.375
<b>609</b>	15.875	10.875	5.125	17	12	5.5
<b>610</b>	16.875	11.688	3.875	18	13	4.25
<b>611</b>	16.875	11.688	5	18	13	5.375
<b>612</b>	16.875	11.688	6.125	18	13	6.5
<b>705</b>	17.875	12.688	4.375	19	14	4.75
<b>706</b>	17.875	12.75	5.75	19	14	6.25
<b>707</b>	17.875	12.75	7.125	19	14	7.5
<b>802</b>	21.313	14.313	6.625	23	16	7
<b>803</b>	21.313	14.313	9.625	23	16	10
<b>902</b>	25.813	14.313	6.625	27.5	16	7
<b>903</b>	25.813	14.313	9.625	27.5	16	10

## CUSTOM FOAM AND ADDITIONAL SIZES

In addition to Platt's stock cubed foam filled cases, we can furnish custom foam interiors to fit our stock cases. Platt also has many additional case sizes available. For additional information on blow-molded cases, click [here](#) and request *Style Form BM99-1*. For additional molded case sizes, [here](#) and request *Engineering Catalog ENG99-2*.

---

### Notes:

RH = *Recessed Hardware*

WTH = *Wheels and Telescoping Handle*

---

All Platt Foam-Filled cases are filled with layers of cubed foam and a flat cushion in the bottom and convoluted and/or flat cushion in the lid.