

Constant Voltage LED Driver - 12vdc 1.67A 20W



Reliable Technical Data

- Rated Input Voltage: 200-240VAC
- Input Frequency: 50Hz
- Output Power: 20W
- Dimension: L154xW50xH14mm
- Body: PC
- Open Circuit; Short Circuit; Over Load;
- Over Heat Protection

Dimension in mm



- Safety According to EN61347-1, EN61347-2-13
- EMI According to EN55015
- EMS According to EN61000-3-2; EN61000-3-3; EN61547
- Approbation Mark: CE ROHS; TUV; C-Tick



Characteristics

Rated input voltage: AC200-240V 50Hz (power factor measured at AC230V and full load)

Model No.	Constant out voltage	Load	Max output Current	PF	Ta	Tc	LxWxH	Approval
LED-DR-12V-1670-20	12V	0-20W	1.67A	0.5	45°C	80°C	154X50X14	TUV