



by Schneider Electric

List Price \$669.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

Technical Characteristics

Ampere Rating	20A
Fixed Trip Setting	Hold: 270A - Trip: 875A
Frame Type	E-Frame
HACR Rated	Yes
Mounting Type	Bolt-On
Voltage Rating	480Y/277Vac
Approvals	UL Listed - CSA Certified
Features	VISI-TRIP trip indication
General Application	Provides overload and short circuit protection
For Use With	NF Panelboards
Interrupting Rating	18kA
Terminal Type	Lugs
Type	EDB
Number of Poles	3-Pole
Depth	4.05 Inches
Width	2.94 Inches
Wire Size	#12 to #6 AWG(Al) - #14 to #6 AWG(Cu)
Height	5.66 Inches

Shipping and Ordering

Category	00931 - Circuit Breakers, Thermal Magnetic, 480Y/247 Vac, Type EDB, UL, Bolt-On
Discount Schedule	DE2
GTIN	00785901875246
Package Quantity	1
Weight	3.55 lbs.
Availability Code	Stock Item: This item is normally stocked in our distribution facility.
Returnability	Y
Country of Origin	MX

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.