



by Schneider Electric

List Price \$669.00 USD

Availability **Stock Item: This item is normally stocked in our distribution facility.**

### Technical Characteristics

|                     |  |
|---------------------|--|
| Ampere Rating       | 40A  |
| Fixed Trip Setting  | Hold: 630A - Trip: 1800A                       |
| Frame Type          | E-Frame  |
| HACR Rated          | Yes  |
| Mounting Type       | Bolt-On  |
| Voltage Rating      | 480Y/277Vac                                    |
| Approvals           | UL Listed - CSA Certified                      |
| Features            | VISI-TRIP trip indication                      |
| General Application | Provides overload and short circuit protection |
| For Use With        | NF Panelboards                                 |
| Number of Poles     | 3-Pole   |
| Interrupting Rating | 18kA   |
| Terminal Type       | Lugs   |
| Type                | EDB  |
| Depth               | 4.05 Inches                                    |
| Wire Size           | #12 to #2/0 AWG(Al) - #14 to #2/0 AWG(Cu)      |
| Height              | 5.66 Inches                                    |
| Width               | 2.94 Inches                                    |

### Shipping and Ordering

|                   |   |
|-------------------|---|
| Category          | 00931 - Circuit Breakers, Thermal Magnetic, 480Y/247 Vac, Type EDB, UL, Bolt-On |
| Discount Schedule | DE2   |
| GTIN              | 00785901875284  |
| Package Quantity  | 1   |
| Weight            | 3.68 lbs.   |
| Availability Code | Stock Item: This item is normally stocked in our distribution facility.         |
| Returnability     | Y   |
| Country of Origin | MX  |

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.