



Hellermann Electric

Pennycross Close, Plymouth, Devon, England PL2 3NX
 Telephone: Plymouth 01752 701261
 Fax: 01752 790058

Product Data Sheet 23

Hellerine Lubricant

Hellerine M is fungistatic lubricating oil designed to dry slowly so that the components stay lubricated longer offering a wider scope for planning assembly procedures for cable locking work.

Hellerine M is ideal for lubricating most rubber and plastic cable markers. It has many other uses where the assembled product can tolerate traces of residue lubricant.

The fungistatic properties of this material are essential when electrical equipment is intended for use under tropical conditions.

Supplied in quantities of 5 litre, 284 ml or 2 dram.

Typical Properties

Specific gravity:	0.88-0.90
Redwood viscosity:	137.3-165.3
Dielectric strength:	9.4KV/mm
Shelf life:	5 years
Continuous Operating Temperature:	-10°C to +150°C
Flash Point:	+180°C

Hellerine Lubricant Grade M is approved under AFS. No 611A (DTD900/4877)

Issue 2 - October 1996

